
## AT1121, AT1123 X-ray and gamma radiation dosimeters

## Photon radiation energy range 15 keV – 10 MeV

Radiation type	AT1121		AT1123	
	H*(10)	H*(10)	H*(10)	H*(10)
X-ray	+	+	+	+
Gamma	+	+	+	+
Bremsstrahlung	+	+	+	+
Continuous long-term	+	+	+	+
Continuous short-term	+	+	+	+
Pulsed	-	-	+	+
Beta (detection)	+	+	+	+

Portable multifunctional wide-range instruments for X-ray and gamma radiation dosimetry of the following types:

- Continuous long-term radiation
- Continuous short-term radiation
- Pulse radiation [AT1123]



The primary function of these dosimeters is the X-ray and gamma radiation dosimetry in wide ranges of ambient dose equivalent rate and energy. Additional functions are the detection of sources of soft and hard gamma radiation, beta emitters, measurement of pulsed and short-term radiation with exposure time estimation, as well as measurement of moving sources of radiation.

It is possible to select one of the four averaging modes during dose rate or dose measurement of continuous X-ray and gamma radiation to operate the dosimeter as a:

- Portable measuring device
- Instrument for laboratory measurements
- Instrument for fixed use
- Instrument for measurement of vehicles.

The dosimeters feature manual and automatic recording of measurement results with date and time into non-volatile memory (the "Notebook") with subsequent data transfer and processing in a PC. The manual mode can store up to 999 measurement results, the automatic mode – more than 500,000.

The dosimeters provide continuous and automatic health monitoring during operation.

Remote control and external alarm units can be attached to the dosimeters for remote monitoring applications.





### **Applications**

- X-ray diagnostics
- Nuclear medicine
- Radiology
- X-ray and gamma-ray flaw detection
- X-ray and gamma-ray testing
- Search X-ray and accelerating apparatus
- Radiation accidents
- Radiation monitoring
- Nuclear industry
- Accelerating installations
- Research activities

#### **Features**

- Tissue-equivalent detector scintillation plastic
- High sensitivity results in rapid measurements with good statistical confidence
- Wide measurement range with 8 orders of magnitude and more
- Wide energy range starting from 15 keV
- Measurement of short-term exposure dose rate and time (from 0.03 s) for continuous radiation
- Measurement of average dose rate of pulse radiation with duration from 10 ns [AT1123]
- One of four available averaging modes is selectable
- Manual and automatic recording of measurement results with date and time into non-volatile memory is provided
- Large dedicated digital/analogue LCD screen with backlighting
- Integrated system for LED measurement path stabilization
- Sound and visual alarm in case threshold level is exceeded
- Remote control is available for remote measurement
- Fixed installation option with external audiovisual alarm with four groups of potential-free contacts for actuator control
- Connection to PC is available in order to create a continuous monitoring system with documenting function
- Tree types of power sources
- Severe operating conditions






# AT1121, AT1123 X-ray and gamma radiation dosimeters


S	na	cifi	cati	on
3	pe	CITI	cati	on

Specification					
Detector	Scintillation plastic, Ø30x15 mm				
Ambient dose equivalent rate measurement range					
Continuous long-term radiation AT1121, AT1123	50 nSv/h 10 Sv/h				
Continuous short-term radiation AT1121, AT1123 Pulse radiation	5 μSv/h 10 Sv/h				
AT1123	0.1 μSv/h 10 Sv/h				
Ambient dose equivalent measurement range	0.1 nSv 100 Sv				
Energy range Continuous long-term and short-term radiation Pulse radiation (AT1123)	15 keV 10 MeV 15 keV 10 MeV				
Energy dependence relative to 662 keV ( <sup>137</sup> Cs) 15 60 keV (with protection cap "0.025 – 3 MeV") 60 keV 3 MeV (with protection cap "0.025 – 3 MeV") 60 keV 10 MeV (with protection cap "0.06 – 10 MeV") 10 20 MeV * (with protection cap "0.06 – 10 MeV")					
Minimum duration of pulse radiation for pulse dose rate up to 1.3 Sv/s (AT1123)	10 ns				
Minimum duration of continuous short-term radiation	0.03 s				
Intrinsic relative measurement error Continuous long-term and short-term radiation Pulse radiation (AT1123)	±15% max. ±30% max.				
Typical sensitivity to <sup>137</sup> Cs gamma radiation	70 cps/(μSv·h <sup>-1</sup> )				
Response time for dose rate change from 0.1 to 1 µSv/h (accuracy error ≤±10%)	<2 s				
Time of <sup>137</sup> Cs gamma radiation dose rate measurement with statistical error ±15% (P=0.95) for the following dose rate:					
50 nSv/h	≤60 s				
0.3 μSv/h	≤10 s				
over 2 μSv/h (Up to 10 Sv/h)	≤2 s				
<b>Typical sensitivity</b> to associated beta radiation of <sup>90</sup> Sr + <sup>90</sup> Y with filter (with protection cap "0.06 – 10 MeV") at 5 cm distance	3·10 <sup>-7</sup> μSv·h <sup>-1</sup> ·Bq <sup>-1</sup>				
Burn-up life	≥100 Sv				
Operation mode setup time	1 min				
Power supply and continuous run time Alternate or direct current mains Built-in rechargeable Ni-MN battery AT1121	≥24 h ≥24 h				
AT1123	≥12 h				
Protection class	IP54				

	Working temperature range	-30°C +50°C	
-	Relative humidity with air temperature ≤35°C without condensation	≤95%	
	Overall dimensions	233x85x67 mm	
	Weight	0.9 kg	



(\*Energy dependence in 10 ... 20 MeV range is based on Monte Carlo method and is for reference only)



Normal dosimeter anisotropy for horisontal plane

The X-ray and gamma radiation dosimeters comply with: GOST 27451-87

Safety requirements of IEC 61010-1:2010, EMC requirements of EN 55011:2009, IEC 61000-4-2:2008, IEC 61000-4-3:2008, IEC 61000-4-4:2004, IEC 61000-4-5:2005, IEC 61000-4-6:2008, IEC 61000-4-11:2004



Design and specifications are subject to change without notice



5 Gikalo st., Minsk 220005, Republic of Belarus Tel./Fax: +375-17-270-81-42 E-mail: info@atomtex.com



